







# **Dry Cabinet**





#### **Outstanding performance**

The XSD series has an outstanding performance for drying moisture sensitive components and pcb's.

The dynamic drying unit of the 5000 series reaches very reliable low humidity values of ≤0,5%RH and automatically regenerates if necessary.

As a result of an insulated double metal sandwich construction a precise temperature of  $60^{\circ}\text{C}$  can be reached with a very low power consumption.

A radial fan and heater supports the drying process and realizes an equable temperature and moisture level in the cabinet. The relevant process data is obtained by use of an accurate Rotronic sensor.







Totech Europe BV
De Linge 28
8253 PJ Dronten

www.superdry-totech.com

Fax: +31 (0) 321 330254 K.v.K.: Lelystad 390 86417 e-mail: sales@totech.eu

Phone: +31 (0) 321 330239

V.A.T.: NL813341887B01 IBAN: NL83Rabo0145683443

BIC: RaboNL2U





A Member of the ASYS Group

#### **Standard features**

**ESD** features

√ User friendly handling Touchscreen display with easy menu structure

Norm (IEC 61340-5-1) ESD stainless steel body (<10<sup>3</sup> Ohm/sq)

Conductive glazing (in- and outside 10<sup>3</sup> Ohm/sq) Insulation 60 mm sandwich construction with Polyurethane

Online functionality Interface and data logging through standard Ethernet interface

Compatible with new MSL 2.0 software

Door & humidity alarm buzzer Longer door openings are detected, high RH levels are detected √ Leveling out Adjustable legs

Lockable doors Every door can be locked separately with a key.

Shelves In height adjustable sliding shelves (5 pcs)

U-5000 series drying unit ≤0,5% RH, made in Germany

**Rotronic sensor** Precision sensor, accuracy +/- 0,8 % RH, +/- 0,3°C

**Power supply** Power cord 5 meter with IEC plug

#### **Benefits**

Network

**European Quality** 

**Drying time (see reference table)** Fast drying time, Level 3 component, <1,4 mm = 18 hours (60°C / 1% RH)

Recovery time after door opening < 6 minutes

**Temperature stability** The same temperature level throughout the drying cabinet as a result of the use of a radial fan in combination with ventilation

and heating canal in an insulated sandwich construction

Temperature setting Heating up to 40°C (optional to 60°C), accuracy +/- 2°C

**Energy saving consumption** As a result of a Dynamic dry unit, sandwich construction with insulating Polyurethane.

Made in Germany

Standard ethernet interface

IPC According to IPC-Jstd 033C

**Maintenance** Easy to service, low maintenance

Totech Europe BV De Linge 28 8253 PJ Dronten www.superdry-totech.com

Fax: +31 (0) 321 330254 K.v.K.: Lelystad 390 86417 e-mail: sales@totech.eu

Phone: +31 (0) 321 330239

BIC: RaboNI2U Bank: Rabobank 14.56.83.443

V.A.T.: NL813341887B01

IBAN: NL83Rabo0145683443



A Member of the ASYS Group

#### **Technical data cabinet**

√ External dimensions: (W x H x D) 700 x 1930/2110 x 808 mm ✓ Internal dimensions: (W x H x D) 544 x 1504 x 600 mm

√ Weight: 142 kg √ Weight on shelf: 50 kg

√ Shelves (WxD): 5 pcs, 535 x 550 mm. (max 15 pcs.)

490 L

✓ Volume: ✓ Electric supply: 230 VAC (120 VAC optional)

✓ Power consumption: 450 W/h (60° C) ✓ Protection class: Class 1, hard grounded

✓ Humidity level cabinet: ≤0,5% RH can be reached with drying unit U-5003

✓ Sensor accuracy: +/- 0,8 % RH, +/- 0,3°C

✓ Temperature accuracy: 60° C, +/- 2° C

#### **Technical data type 4 display**

#### **Settings**

- ✓ Language Menu
- ✓ Nominal Value Humidity
- ✓ Humidity Alarm
- ✓ Delay Humidity Alarm
- ✓ Nominal Value Temperature (in combination with heater)
- ✓ Temperature Alarm (in combination with heater)
   ✓ Delay Temperature Alarm (in combination with heater)
- ✓ Sensor Offset
- ✓ Password Protection
- Manual Regeneration

#### **Display**

- ✓ Supply voltage (supplied by drying unit) 24 VAC/DC, 350 mA
- ✓ Input Touchscreen
- ✓ TFT Color LCD 4,3"
- √ Controllable Brightness
- √ Standard Ethernet Interface
- √ USB Interface for data logging purposes



Totech Europe BV De Linge 28 8253 PJ Dronten www.superdry-totech.com Phone: +31 (0) 321 330239 Fax: +31 (0) 321 330254 K.v.K.: Lelystad 390 86417 e-mail: sales@totech.eu

V.A.T.: NI 813341887B01 IBAN: NL83Rabo0145683443

BIC: RaboNI 2U







A Member of the ASYS Group

#### **Technical data Rotronic sensor HC2A-s**



Based on the Airchip 3000 Technology use the HygroClip 2 probes can be used for control of temperature and humidity.

The HygroClip 2 probes can be configured with the ROTRONIC HW4 software and share the following features:

- Measurement of relative humidity and temperature.
- Programmable automatic sensor test with failsafe mode and sensor drift compensation.

#### **Technical data dry-unit U-5000 series**

- ✓ Dehumidifying performance: 120 g/h max.✓ Minimal humidity 0,2% RH
- ✓ Dehumidifying Temperature 10 60° C
- √ Electric supply: 230 VAC
- √ Dimensions (L x B x H): 487 x 487 x 150 mm
- √ Weight: 14 kg



Totech Europe BV De Linge 28 8253 PJ Dronten www.superdry-totech.com Phone: +31 (0) 321 330239 Fax: +31 (0) 321 330254 K.v.K.: Lelystad 390 86417 e-mail: sales@totech.eu

V.A.T.: NL813341887B01 IBAN: NL83Rabo0145683443 BIC: RaboNL2U






A Member of the ASYS Group

#### **Free Totech viewer**

- √ Writing of climate data, door openings and alarms to SD card
- √ Transfer data through Ethernet to PC (history data)
- √ User-friendly display of all relevant data
- ✓ Data processing in MS-Excel
- ✓ Seamless documentation
- √ Excellent process safety



Totech Europe BV

De Linge 28

8253 PJ Dronten

www.superdry-totech.com

Phone: +31 (0) 321 330239 Fax: +31 (0) 321 330254 K.v.K.: Lelystad 390 86417 e-mail: sales@totech.eu V.A.T.: NL813341887B01 IBAN: NL83Rabo0145683443


BIC: RaboNL2U





A Member of the ASYS Group

#### **Performance test**



#### **Test conditions**

✓ Type of dew point sensor: 9x Hygroclip HC2A-S

✓ Accuracy of dew point sensor:  $\pm 0.3^{\circ}$  C at  $+ 20^{\circ}$  C ( $+ 68^{\circ}$  F)

√ Location of sensors: Every corner + center

✓ Ambient conditions: Hum.  $50 \pm 5\%$  rH, 22°C  $\pm 2$ °C, Pressure  $994 \pm 20$  hPa

✓ Door openings: 2 door openings, 15 sec.

For more detailed test results, please refer to our website.

Totech Europe BV

De Linge 28

8253 PJ Dronten

www.superdry-totech.com

Phone: +31 (0) 321 330239 Fax: +31 (0) 321 330254 K.v.K.: Lelystad 390 86417 e-mail: sales@totech.eu V.A.T.: NL813341887B01 IBAN: NL83Rabo0145683443


BIC: RaboNL2U





A Member of the ASYS Group

## **Technical drawings**



Dimensions mentioned in mm.

#### **Shelves**

Number of different types of shelves that can be mounted in the cabinet

Number of shelves (47000136)	5	6	7	8	9	10	11	12	13	14	15
Distance (in mm) between shelves if equally divided	280	230	180	180	130	130	80	80	80	80	80
Remaining space between top shelf and top cabinet	330	285	330	140	330	185	430	380	330	235	140

Number of shelves (47000140)	5	6	7	8	9	10	11	12	13	14	15
Distance (in mm) between shelves if equally divided	260	210	165	165	115	115	70	70	70	70	70
Remaining space between top shelf and top cabinet	235	190	235	40	235	90	430	330	235	140	40

Number of drawers	1	2	3	4	5	6	7	8	9	10	11	12	13	14	15
Remaining space in mm	1366	1270	1174	1078	982	886	790	694	598	502	406	310	214	118	22

Totech Europe BV

De Linge 28

8253 PJ Dronten

www.superdry-totech.com

Phone: +31 (0) 321 330239 Fax: +31 (0) 321 330254 K.v.K.: Lelystad 390 86417 e-mail: sales@totech.eu

IBAN: NL83Rabo0145683443 BIC: RaboNL2U

Bank: Rabobank 14.56.83.443


V.A.T.: NL813341887B01





A Member of the ASYS Group

## **Technical drawings**



Totech Europe BV

De Linge 28

8253 PJ Dronten

www.superdry-totech.com

Phone: +31 (0) 321 330239 Fax: +31 (0) 321 330254 K.v.K.: Lelystad 390 86417 e-mail: sales@totech.eu V.A.T.: NL813341887B01 IBAN: NL83Rabo0145683443


BIC: RaboNL2U





A Member of the ASYS Group

## **Technical drawings**



Totech Europe BV

De Linge 28

8253 PJ Dronten

www.superdry-totech.com

Fax: +31 (0) 321 330254

K.v.K.: Lelystad 390 86417

e-mail: sales@totech.eu

Phone: +31 (0) 321 330239

V.A.T.: NL813341887B01 IBAN: NL83Rabo0145683443

BIC: RaboNL2U





# SUPER DRY® Totech EU®


## **Options**



#### **SMD Reel rack with reel supports**

L x W =  $530 \times 265 \text{ mm}$  incl. 18 reel supports.

Item number 20014005



#### **Reel support**

Additional reel supports for 20014005.

Item number 20014201



#### Door release pedal

These foot pedals enable you to open the doors keeping your hands free

Item number 47000146



#### **Humidity alarm signal lamp**

Two-color (orange/green or red/green), magnetically fixed, providing optical signals on operational states and exceeded limit values. Operates on 24V.

Item number 20016030



#### N<sup>2</sup> Autoflow system

The autoflow system is developed to use in combination with a Totech drying cabinet. The device is used for the quick removal of moisture in the cabinet after the door has been opened. The drying pocess is realised by using nitrogen  $(N^2)$ , which is added automatically after the door has been closed. (by means of adjustable timer function).

Item number 22613066

Totech Europe BV

De Linge 28

8253 PJ Dronten

www.superdry-totech.com

Phone: +31 (0) 321 330239 Fax: +31 (0) 321 330254 K.v.K.: Lelystad 390 86417

K.v.K.: Lelystad 390 86417 e-mail: sales@totech.eu IBAN: NL83Rabo0145683443
BIC: RaboNI 2U

V.A.T.: NL813341887B01





A Member of the ASYS Group

## **Options**



#### **Additional shelves**

Stainless steel shelf without rollers.

Item number 47000136



#### **Additional sliding shelves**

Stainless steel sliding shelf on metal rollers, 100% extractable

Item number 47000140



#### Drawer

Stainless steel drawer

Item number 47000127



#### **Divider system drawer**

Stainless steel divider system which enables you to create compartments with a minimum measurement of  $+-2.5 \times 2.5 \text{ cm}$  or a multiple of 2.5 cm. A standard set contains 5 long strips (553 mm) and 5 short strips (502 mm).

Item number 4700129



## **Cover plate for XSD shelves**

Prevent small items to fall through

Item number 47000132

Totech Europe BV

De Linge 28

8253 PJ Dronten

www.superdry-totech.com

Phone: +31 (0) 321 330239 Fax: +31 (0) 321 330254 K.v.K.: Lelystad 390 86417

K.v.K.: Lelystad 390 86417 e-mail: sales@totech.eu V.A.T.: NL813341887B01 IBAN: NL83Rabo0145683443

BIC: RaboNL2U





A Member of the ASYS Group

## **Options**



#### **Honeycomb system**

Flexible stainless steel storage system for IC Tubes components and PCB's. The width of the compartments is adjustable before installing the system in the cabinet. The number of compartments variates from 17 till 170. In total 4 systems can be installed in a cabinet.

Item number 20050100



#### X Feeder system

This feeder rack is suitable for Siemens X Feeder systems. Sold in combination with reel rack.

Item number 46204004



#### **S Feeder system**

This feeder rack is suitable for S Feeder systems. Sold in combination with reel rack.

Item number 46204009



#### **Hygroclip 2**

Probe with maximum accuracy for all climate measurements.

Item number 470000027

Excange calibrated sensor: *Item number 47000040* 



### **Humidity calibrator Hygropalm 22**

Precision measuring device for calibrating sensors.

Set including Hygroclip sensor, case and cable: *Item number 20001019* Hygropalm only: *Item number 20001016* 

Totech Europe BV

De Linge 28

8253 PJ Dronten

www.superdry-totech.com

Phone: +31 (0) 321 330239

Fax: +31 (0) 321 330254

K.v.K.: Lelystad 390 86417

e-mail: sales@totech.eu

V.A.T.: NL813341887B01 IBAN: NL83Rabo0145683443

BIC: RaboNL2U







## **Options**



#### MSL 2.0 software for 1000 components

Software solution for the monitoring of moisture sensitive components and their MSL states during storage and processing in the production. The exact drying state individually for each component is monitored and displayed with the software. One of the possibilities is that it can read out multiple HC2A-S sensors. To adjust storage conditions, picking of stock, removal of used parts and more stock control. A complete history for each component is traceable up to the full processing. The evaluation of the drying conditions is based on the requirements of the IPC / JEDEC J-STD-033B1 directive.


Item number 20010036



#### MSL software upgrade with additional 1000 components

Upgrade to monitor an additional 1000 components


Item number 200174502



#### **Totech Monitor software**

Realtime cabinet monitoring with alarm function, sending e-mails with detailed information on the status of the cabinet. History data files with graphical overview

Item number 47000583



#### **Upgrade for 60°C**

Heater 60°C for XSDB

Item number 21001505



#### **Touchscreen display 7 inch**

Bigger 7" touchscreen display

Item number 30022222

v17.12

Totech Europe BV De Linge 28 8253 PJ Dronten www.superdry-totech.com Phone: +31 (0) 321 330239 Fax: +31 (0) 321 330254 K.v.K.: Lelystad 390 86417 e-mail: sales@totech.eu

V.A.T.: NL813341887B01 IBAN: NL83Rabo0145683443

BIC: RaboNI2U

